



## PB SERIES

PB SERIES	PEDESTAL ONLY	PB SERIES	PEDESTAL + U-PH5 (BC-PH5)* (BOTTOM SLOPE CORRECTOR + 9/16")	PB SERIES	PEDESTAL + U-PH5* + KIT 5 (FIXED JOIST HOLDER)	PB SERIES	PEDESTAL + U-PH5* + KIT 2 (ADJUSTABLE JOIST HOLDER)
		(OR) PEDS+KIT5 FIXED JOIST HOLDERS+U-PH5 SLOPE CORRECTORS.				USE LONG PLUG AND PIN TO ATTACH KIT-2 (+ 7/16")	
■ U-TAB + U-PAD	1/8" to 3/8"						
⊗ BC 0 (FIXED HEIGHT PEDESTAL)	7/16"	● BC 0 (FIXED HEIGHT PEDESTAL) + U-PH5	1"	● BC 0 (FIXED HEIGHT PEDESTAL) + U-PH5 + KIT 5	1"		
⊗ BC 1 (FIXED HEIGHT PEDESTAL)	9/16"	● BC 1 (FIXED HEIGHT PEDESTAL) + U-PH5	1-1/8"	● BC 1 (FIXED HEIGHT PEDESTAL) + U-PH5 + KIT 5	1-1/8"		
⊗ BC 0 (x2 STACKED)	3/4"	● BC 0 (x2 STACKED) + U-PH5	1-5/16"	● BC 0 (x2 STACKED) + U-PH5 + KIT 5	1-5/16"		
⊗ BC 0 (x3 STACKED)	1-1/16"	● BC 0 (x3 STACKED) + U-PH5	1-5/8"	● BC 0 (x3 STACKED) + U-PH5 + KIT 5	1-5/8"		
⊗ PB 01	1-1/8" to 1-5/8"	● PB 01 + U-PH5	1-11/16" to 2-3/16"	● PB 01 + U-PH5 + KIT 5	1-11/16" to 2-3/16"	● PB 01 + U-PH5 + KIT 2	2-1/8" to 2-5/8"
● PB 1	1-5/8" to 2-3/8"	● PB 1 + U-PH5	2-3/16" to 2-15/16"	● PB 1 + U-PH5 + KIT 5	2-3/16" to 2-15/16"	● PB 1 + U-PH5 + KIT 2	2-5/8" to 3-3/8"
● PB 2	2-3/8" to 3-1/2"	● PB 2 + U-PH5	2-15/16" to 4 1/16"	● PB 2 + U-PH5 + KIT 5	2-15/16" to 4 1/16"	● PB 2 + U-PH5 + KIT 2	3-3/8" to 4-1/2"
● PB 3	3-1/2" to 5-3/4"	● PB 3 + U-PH5	4 1/16" to 6-5/16"	● PB 3 + U-PH5 + KIT 5	4 1/16" to 6-5/16"	● PB 3 + U-PH5 + KIT 2	4-1/2" to 6-3/4"
● PB 4	5-3/4" to 9-3/4"	● PB 4 + U-PH5	6-5/16" to 10-5/16"	● PB 4 + U-PH5 + KIT 5	6-5/16" to 10-5/16"	● PB 4 + U-PH5 + KIT 2	6-3/4" to 10-3/4"
⊗ C1-B4 (COUPLER)	ADDS 3-1/4" to 4-3/4"	○ -	-	○ -	-	○ -	-
⊗ C2-B4 (COUPLER)	ADDS 7-11/16" to 9-1/4"	○ -	-	○ -	-	○ -	-
● PB 5 (PB-4 + PB-3 + x1 C1) **	9-1/16" to 12-3/8"	● PB 5 (PB-4 + PB-3 + x1 C1) + U-PH5 **	9-5/8" to 12-15/16"	● PB 5 (PB-4 + PB-3 + x1 C1) + U-PH5 + KIT 5 **	9-5/8" to 12-15/16"	● PB 5 (PB-4 + PB-3 + x1 C1) + U-PH5 + KIT 2 **	10-1/16" to 13-3/8"
● PB 6 (PB 4 + x1 C1)	11-1/8" to 14-7/16"	● PB 6 (PB 4 + x1 C1) + U-PH5	11-11/16" to 15"	● PB 6 (PB 4 + x1 C1) + U-PH5 + KIT 5	11-11/16" to 15"	● PB 6 (PB 4 + x1 C1) + U-PH5 + KIT 2	12-1/8" to 15-7/16"
● PB 7 (PB 4 + x1 C2)	14-7/16" to 19-3/16"	● PB 7 (PB 4 + x1 C2) + U-PH5	15" to 19-3/4"	● PB 7 (PB 4 + x1 C2) + U-PH5 + KIT 5	15" to 19-3/4"	● PB 7 (PB 4 + x1 C2) + U-PH5 + KIT 2	15-7/16" to 20-3/16"
● PB 8 (PB 4 + x1 C1 + x1 C2)	17-13/16" to 23-7/8"	● PB 8 (PB 4 + x1 C1 + x1 C2) + U-PH5	18-3/8" to 24-7/16"	● PB 8 (PB 4 + x1 C1 + x1 C2) + U-PH5 + KIT 5	18-3/8" to 24-7/16"	● PB 8 (PB 4 + x1 C1 + x1 C2) + U-PH5 + KIT 2	18-13/16" to 24-7/8"
● PB 9 (PB 4 + x2 C2)	21-1/16" to 28-5/8"	● PB 9 (PB 4 + x2 C2) + U-PH5	21-5/8" to 29-3/16"	● PB 9 (PB 4 + x2 C2) + U-PH5 + KIT 5	21-5/8" to 29-3/16"	● PB 9 (PB 4 + x2 C2) + U-PH5 + KIT 2	22-1/16" to 29-5/8"
● PB 10 (PB 4 + x1 C1 + x2 C2)	24-3/8" to 33-3/8"	● PB 10 (PB 4 + x1 C1 + x2 C2) + U-PH5	24-15/16" to 33-15/16"	● PB 10 (PB 4 + x1 C1 + x2 C2) + U-PH5 + KIT 5	24-15/16" to 33-15/16"	● PB 10 (PB 4 + x1 C1 + x2 C2) + U-PH5 + KIT 2	25-3/8" to 34-3/8"
● PB 11 (PB 4 + x3 C2)	27-3/4" to 38-1/8"	● PB 11 (PB 4 + x3 C2) + U-PH5	28-5/16" to 38-11/16"	● PB 11 (PB 4 + x3 C2) + U-PH5 + KIT 5	28-5/16" to 38-11/16"	● PB 11 (PB 4 + x3 C2) + U-PH5 + KIT 2	28-3/4" to 39-1/8"

5-10% SLOPE: x2 U-PH5 SLOPE CORRECTORS + x1 BC-1 + 1"

10-15% SLOPE: x3 U-PH5 SLOPE CORRECTORS + x2 BC-1 + 2"

\* Buzon BC-PH5 Bottom Slope Correctors used for steeper slopes (multiple correctors) up to 20%

USE PIN TO ATTACH BC-1 TO BOTTOM SLOPE CORRECTOR; AND LONG PLUG AND PIN TO ATTACH TOP SLOPE CORRECTOR TO BC-1

FOR RAMPS: Use the BC-Series Pedestals with PH5 Top Slope Correctors

PB 5 (PB-4 + PB-3 + x1 C1) ADDS: 9-1/16" to 12-3/8"